



Adhesive Prepregs for Composite Manufacturers, LLC

DA 4518U Unidirectional Carbon Epoxy Prepreg System

DESCRIPTION

DA 4518U is a tough, versatile, modified epoxy resin system that cures at 250°F to 350°F. DA4518U can be supplied as a prepreg tape coated on unidirectional graphite.

PHYSICAL PROPERTIES

Weight:	0.060 lbs./sq ft
Resin Content:	38% by Weight
Volatiles:	Less than 1%
Tack: Medium	
Resin Flow:	24% average
Gel Time:	10 minutes at 250°F
Shelf Life:	One year at 0°F
Six months at 40°F	
Twenty days at 75°F	
Standard Roll:	per customer request.

MECHANICAL PROPERTIES

Cure Cycle:	Press cured for one hour at 250°F and 50 psi
pressure	
Thickness:	0.006 inch/ply
Resin Content:	38% by Weight
Flexural Strength	(ASTM D 790) 226 Ksi
Flexural Modulus	(ASTM D 790) 18.1 Msi
Beam Shear	(ASTM D 2344) 14.1 Msi
Tensile Strength	(ASTM D 3039) 310 Ksi
Tensile Modulus	(ASTM D 3039) 18.8 Msi

ADHESIVE PREPREGS FOR COMPOSITES MANUFACTURERS
P.O. BOX 264 1366 NORWICH RD. PLAINFIELD CT 06374
PHONE 860-564-7817 FAX 860-564-1535 www.prepregs.com

DA4518U UniCarbon

CURE CYCLE

DA 4518 is designed to cure in one hour at 250°F (121°C), however this system may be cured at 250°F for one hour and a post cure of 350°F for one hour. The prepreg may be cured using either standard heat-up methods or by in-hot, out-hot press applications. A pressure of 30 psi is recommended, however pressures of 10 to 50 psi may be used.

STORAGE

Store material in a contaminate free container and store at 0 degrees F for extended storage. For shorter storage time requirements store at 40 degrees F, this enables quicker stabilization times.

APPLICATION

Remove material from cold storage at least 20 hours prior to use to allow for stabilization at room temperature. Keep the material wrapped to prevent moisture from condensing on the adhesive. If details are cut and replaced into cold storage, shorter stabilization times may be used.

Cut the material to size, remove the release paper and apply to part or mold. Remove the separator paper and join the parts together. Parts are now ready to be bonded and may be cured in a press, autoclave, or vacuum bag in an oven. Apply at least 30 psi pressure..

CLEAN UP

The adhesive can be removed from non-bonding areas with ketones or methylene chloride. Be sure to follow all Material Safety Data Sheet (MSDS) guidelines for the solvent to be used.

CAUTION

This material contains epoxy resins and amines which may cause irritation to sensitive skin. Avoid contact with eyes or skin. If contact with skin occurs, wash as soon as possible with soap and water. If contact with eyes occurs, flush with water for 15 minutes. Do not handle or use this material until Material Safety Data Sheet has been read and understood. The user of this material is required to use the necessary protective equipment as directed by applicable state and federal laws when handling, curing, and grinding this material.

IMPORTANT NOTICE

Information in this data sheet has been obtained under controlled laboratory conditions and is believed to be accurate. Properties listed are typical values and are not intended for use in preparing specifications. Actual values may vary. No warranty is expressed or implied for which APCM assumes legal responsibility. APCM cannot be responsible for misapplication or handling and use under conditions beyond its control and under no circumstances shall be liable for incidental or consequential damage resulting from handling or use of this material.

ADHESIVE PREPREGS FOR COMPOSITES MANUFACTURERS
P.O. BOX 264 1366 NORWICH RD. PLAINFIELD CT 06374
PHONE 860-564-7817 FAX 860-564-1535 www.prepregs.com